

CS-Random HS Automatic Case Sealer

It's About the Case

Square Cases! No Jams!

Square cases are the key to successful secondary packaging. Lantech Case Sealers are the key to square cases.



Image shown may not reflect final control and electrical cabinet placement.



High Speed Random Case Sealing

High volume lines with varying case sizes require fast processing in sealing after the product is packed. The Lantech Random High Speed Case Sealer meets this requirements.

Built for flexibility and speed, the CS-Random HS is particularly suitable for manufacturing and distribution sites with multiple packaging lines that merge for sealing.

The CS-Random HS is a customizable production line case sealer, capable of adjusting via upstream signal or photo eyes to handle different size cases from multiple product lines.



How Lantech Case Sealers Make Square Cases

Controlling the case throughout the sealing process is the secret to keeping the case square.

Lantech case sealers establish control immediately with adjustable infeed guides that introduce the case into spring loaded side belts.

Our 2 stage front flap folding system ensures the leading top flap folds at the score line. Stage 2 folds the flap perpendicular to the case so the top side flaps will be horizontal when they are closed.

The trailing top flap is precisely folded and an active long flap folding system folds the top side flaps and hold them down to be sealed in that position.

Lantech case sealers preserve the effort and investment you have made in sealing a case properly.



Random Case Handling

Upstream case dimensions communication with the case sealer. The machine will adjust automatically to the presented incoming cases.



Guided Case Entry

Automatic adjustable infeed guides ensure correct infeed with proper distance between cases, no jams.



Smooth Case Transit

Spring loaded side belts hold cases firmly throughout the sealing cycle. Rollers support the cases as they move through the sealer.




Pre-Folding of Front Short Flap

Pre folding of the leading short flaps helps avoiding packaging damage and improves the reliability of your packaging process.




Controlled Long Flap Folding

During the transit the long top flaps are folded down and will be kept in place until entering the closing unit.



Precise Top Closing

After closing the top flaps are sealed with tape or glue.



*Right side flow version shown. Left side flow version available.
*Image shown may not reflect final control panel and electrical cabinet placement.

CS-Random HS Case Sealer

Standard Specifications - options available

SPEC ITEM	TAPE	HOTMELT
Speed	Up to 25 cases per minute Options and application can change the speed	Up to 17 cases per minute Options and application can change the speed
Minimum Case Outer Dimensions	200 mm L x 150 mm W x 120 mm H (7 7/8" L x 5 15/16" W x 4 3/4" H)	200 mm L x 150 mm W x 150 mm H (7 7/8" L x 5 15/16" W x 5 15/16" H)
Maximum Case Outer Dimensions	620 mm L x 510 mm W x 500 mm H (24 2/5" L x 20 1/8" W x 19 11/16" H)	
Case Type	RSC, HSC, FEFCO 0201	
Flute Type	B, C, E	
Wall Type	Single and Double	
Sealing Device	Standard Lantech® TH-Series Tape Head	Optional Hotmelt Robatech
Dimensions -Machine	3200 mm L x 1100 mm W x 2100 mm H (126" L x 43 5/8" W x 82 3/8" H)	
Electrical Service	3L-PE-400V-50Hz Neutral 230V, 3-ph, 60Hz, Wye w/Ground	
Pneumatics	6 Bar (80 PSI)	

Click or Scan to Learn More



Product
Video



By-Pass
Function



Lantech.com